

name:


PUMPS

SKU:


SZ001-3

description:

The device affects the construction of the muscles of the chest, shoulders, arms and trunk muscles.



terms of use:



MAX
160kg

dimensions (L x W x H):

380 x 230 x 70 cm

safety zone:

680 x 530 cm

technical specifications:

- Four wooden horizontal beams mounted at different heights to the posts \varnothing 60 mm and 3 mm thick, made from stainless steel and hot-galvanized
- The thickness of the wooden beam: 10 x 15 cm
- The posts fixed in the ground for concrete foundations: 0.4 x 0.4 x 0.7 m
- Impregnated surface
- Wood is FSC certified (Forest Stewardship Council) - comes from controlled cultivation, carried out in accordance with the global forests protection program
- It is recommended to use a rubber or paved surface under the hands

installation:

1. Determine with the investor (or his representative) the place of installation and clear the area.
2. Dig pits under the footings according to recommendations of the supplier and guidelines of the relevant standard.
3. Place the device in dug pits, re-level and pour the foundation (B25), re-level again.
4. When the concrete is bound (after minimum 24 hours, depends on weather conditions and time of year), check the stability of the device.
5. Clean up the area.